



## Eaton 248440

Eaton Distribution parts. Auxiliary contact,  
for PLHT/AZ, 1N/O+1N/C, 0.5HP

### □□□□

<b>PRODUCT NAME</b>	Eaton Distribution parts
<b>CATALOG NUMBER</b>	248440
<b>PRODUCT LENGTH/DEPTH</b>	80 mm
<b>PRODUCT HEIGHT</b>	75 mm
<b>PRODUCT WIDTH</b>	8.8 mm
<b>PRODUCT WEIGHT</b>	0.041 kg
<b>COMPLIANCES</b>	RoHS conform
<b>CERTIFICATIONS</b>	EN45545-2 IEC 61373

USED WITH	Auxiliary contacts Accessory for miniature circuit breaker Accessory
ACCESSORY/SPARE PART TYPE	Auxiliary contacts
MOUNTING METHOD	For fitting on right to: AZ, PLHT
ADDITIONAL EQUIPMENT REQUIRED	Auxiliary switch
AMBIENT OPERATING TEMPERATURE - MAX	40 °C
AMBIENT OPERATING TEMPERATURE - MIN	-5 °C
ASSEMBLY WIDTH	0.5 TE
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	1
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	1
NUMBER OF POLES AT MAIN CONTACT UNIT - MAX	2
NUMBER OF SWITCHES (FAULT SIGNAL)	0
VOLTAGE TYPE	AC
FUNCTIONS	Auxiliary switch
DEVICE FITTING	Universal
TYPE	<ul style="list-style-type: none"><li>• Accessory</li><li>• Accessory for miniature circuit breaker</li></ul>
APPLICATION	Switchgear for industrial and advanced commercial applications
RATED OPERATIONAL VOLTAGE (UE) - MAX	230 V
RATED SWITCH CURRENT	6 A
SUITABLE FOR CURRENT OF MAIN CONTACT UNIT - MAX	8 A

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

