



Eaton 24CAV2

Eaton Bussmann series medium auxiliary fuse, VT fuse-link, medium voltage, 2 A, AC 24 kV, 340 x 41.3 mm, back-up, IEC, Protection of auxiliary transformers, 2 A, 40K A Breaking Cap, Inst Air, Back-up, IEC, AC, Class back-up, Bolt-on

□□□□

PRODUCT NAME	Eaton Bussmann series medium auxiliary fuse
CATALOG NUMBER	24CAV2
UPC	051712832915
PRODUCT LENGTH/DEPTH	340 mm
PRODUCT HEIGHT	41 mm
PRODUCT WIDTH	41 mm
PRODUCT WEIGHT	1000 g
CERTIFICATIONS	IEC60282-1

□□□□

□□

AMPERAGE RATING	2 A
FUSE INDICATOR	Non Indicating
FUSE SIZE	340 x 41.3 mm 340 x 41 mm
BREAKING CAPACITY	40 kA
INSTALLATION TECHNIQUE	Air
PERFORMANCE CAT ACCORDING TO IEC 60282-1	Back-up
PRODUCT APPLICATION	Auxiliary transformer protection
RELEASE CHARACTERISTIC	Other
STANDARD	IEC
UTILIZATION CATEGORY	Other
VOLTAGE TYPE	AC
WITH STRIKER	No
CLASS	Class back-up
BARRELS	1
CONSTRUCTION TYPE	Bolt-on
FUSE SHAPE	Cylindrical
FUSE DIAMETER	41 mm
RESISTANCE	2.54 ohms
INTERRUPT RATING	40 kAIC
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION SIZE	340 x 41.3 mm 340 x 41 mm
PACKAGING TYPE	Standard
QUANTITY	1
VOLTAGE RATING	24 kV
TYPE	fuse
APPLICATION	Protection of auxiliary transformers
FUSE TYPE	CAV

