

Eaton 24FDMSJ10

Eaton Bussmann series medium voltage DIN fuse, MV, 10 A, AC 24 kV, 2", 51 x 442 mm, Full range, DIN, with striker

PRODUCT NAME	Eaton Bussmann series medium voltage DIN fuse
CATALOG NUMBER	24FDMSJ10
UPC	051712832922
PRODUCT LENGTH/DEPTH	442 mm
PRODUCT HEIGHT	76 mm
PRODUCT WIDTH	51 mm
PRODUCT WEIGHT	2200 g
COMPLIANCES	DIN 43625 VDE 0670-4 IEC 60282-1
CERTIFICATIONS	ASTA

USED WITH	270303 Fuse clip A3354710 Fuse clip
AMPERAGE RATING	10 A
FUSE INDICATOR	With Striker
FUSE SIZE	51 x 442 mm
BREAKING CAPACITY	35.5 kA
INSTALLATION TECHNIQUE	Air
PERFORMANCE CAT ACCORDING TO IEC 60282-1	Other
PRODUCT APPLICATION	Primary side transformer protection
RATED FREQUENCY - MAX	50 Hz
RATED FREQUENCY - MIN	50 Hz
RELEASE CHARACTERISTIC	Other
STANDARD	DIN
UTILIZATION CATEGORY	Other
VOLTAGE TYPE	AC
WITH STRIKER	Yes
CLASS	Class full-range
PRE ARC (I2T)	2.7 x 100
RESISTANCE	218 Ohms
WATT LOSSES	29 W
FUSE DIAMETER	51 mm
INTERRUPT RATING	35.5 kAIC
CONSTRUCTION SIZE	51 x 442 mm
MOUNTING METHOD	Clip-in
VOLTAGE RATING	24 kV
TYPE	Fuse
APPLICATION	- transformer protection - indoor or outdoor use
FUSE TYPE	FDMSJ



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

