



Eaton 24TXMEJ160

Eaton Bussmann series medium voltage DIN fuse, 160 A, AC 24 kV, 3.5", 88 x 442 mm, backup, DIN, with striker

□□□□

PRODUCT NAME	Eaton Bussmann series medium voltage DIN fuse
CATALOG NUMBER	24TXMEJ160
UPC	051712186391
PRODUCT LENGTH/DEPTH	442 mm
PRODUCT HEIGHT	88 mm
PRODUCT WIDTH	88 mm
PRODUCT WEIGHT	5855 g
COMPLIANCES	DIN 43625 VDE 0670-4 IEC 60282-1
CERTIFICATIONS	UL VDE

AMPERAGE RATING	160 A
FUSE INDICATOR	With Striker
BREAKING CAPACITY	31.5 kA
INSTALLATION TECHNIQUE	Air
PERFORMANCE CAT ACCORDING TO IEC 60282-1	Back-up
PRODUCT APPLICATION	Primary side transformer protection
RATED FREQUENCY - MAX	50 Hz
RATED FREQUENCY - MIN	50 Hz
RELEASE CHARACTERISTIC	Other
STANDARD	DIN
UTILIZATION CATEGORY	Other
VOLTAGE TYPE	AC
WITH STRIKER	Yes
CLASS	Class back-up
BARRELS	1
CONSTRUCTION TYPE	Bolt-on
PRE ARC (I2T)	1.3 x 105
RESISTANCE	9.6 Ohms
WATT LOSSES	515 W
FUSE DIAMETER	76 mm
COLOR	Brown
INTERRUPT RATING	31.5 kAIC
CONSTRUCTION SIZE	88 x 442 mm
MOUNTING METHOD	Clip-in
PACKAGING TYPE	Standard
QUANTITY	1
VOLTAGE RATING	24 kV
TYPE	Fuse
SPECIAL FEATURES	Back-up, Transformer protection, Indoor or outdoor use
APPLICATION	• transformer protection • indoor or outdoor use
FUSE TYPE	TXMEJ

