

Eaton 250NHFF1BI-400

Fuse-link, LV, 250 A, AC 400 V, NH1, gFF, IEC, dual indicator, insulated gripping lugs

PRODUCT NAME	Eaton Bussmann series low voltage NH Fuse
CATALOG NUMBER	250NHFF1BI-400
PRODUCT LENGTH/DEPTH	135 mm
PRODUCT HEIGHT	63 mm
PRODUCT WIDTH	40 mm
PRODUCT WEIGHT	348 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269-1 IEC 60269-2 DIN 43620

AMPERAGE RATING	250 A
FITTED WITH:	Insulated metal gripping lugs
FUSE SIZE	NH1
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
RATED VOLTAGE AC	400 V
CLASS	Class gFF
FUSE TYPE	Square body with knife blade contact
UTILIZATION CATEGORY	gFF(full-range, extra fast operation)
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	Yes
CONNECTION	Blade end
CONSTRUCTION	NH1
CONSTRUCTION SIZE	NH1
FUSE SHAPE	Knife blade contacts Square body
SUITABLE FOR	SD1-D Single pole NH Fuse base Microswitch 170H0236 TD1-D Triple pole NH Fuse base
MATERIAL	Ceramic body
QUANTITY	3
VOLTAGE RATING	400 V
TYPE	fuse
APPLICATION	industrial



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

