

## Eaton 250NHG03B

Eaton Bussmann series low voltage NH Fuse,  
Live gripping lug, 500V, 250A, 120 kAIC,  
Combination fuse status indicator, fuse,  
Blade end connection, Class C gL/gG,  
Square-body with knife blade contact,  
Ceramic body

<b>PRODUCT NAME</b>	Eaton Bussmann series low voltage NH Fuse
<b>CATALOG NUMBER</b>	250NHG03B
<b>UPC</b>	051712626200
<b>PRODUCT LENGTH/DEPTH</b>	150 mm
<b>PRODUCT HEIGHT</b>	71 mm
<b>PRODUCT WIDTH</b>	54 mm
<b>PRODUCT WEIGHT</b>	619.667 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	IEC 60269-1 IEC 60269-2 DIN 43620

AMPERAGE RATING	250 A
FITTED WITH:	Metal gripping lugs
FUSE SIZE	NH03
CURRENT TYPE	AC
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
RATED SWITCHING CAPACITY	120 kA
RATED VOLTAGE AC	500 V
CLASS	Class gG/gL
FUSE TYPE	Square body with knife blade contact
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	Blade end
CONSTRUCTION	NH03
CONSTRUCTION SIZE	NH03
FUSE SHAPE	Knife blade contacts Square body
VOLTAGE TYPE	AC
SUITABLE FOR	Microswitch BVL50
MATERIAL	Ceramic body
QUANTITY	3
VOLTAGE RATING	500 V
TYPE	fuse
SPECIAL FEATURES	Live gripping lug
APPLICATION	<ul style="list-style-type: none"> <li>• industrial</li> <li>• Utilities, Solar, Wind</li> </ul>



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

