

Eaton 250NHG2B-690

Eaton Bussmann series low voltage NH Fuse,
Live gripping lug, 690V, 250A, 120 kAIC,
Combination fuse status indicator, fuse,
Blade end connection, Class C gL/gG,
Square-body with knife blade contact,
Ceramic body

PRODUCT NAME	Eaton Bussmann series low voltage NH Fuse
CATALOG NUMBER	250NHG2B-690
UPC	051712191173
PRODUCT LENGTH/DEPTH	150 mm
PRODUCT HEIGHT	71 mm
PRODUCT WIDTH	54 mm
PRODUCT WEIGHT	0.097 kg
COMPLIANCES	RoHS Compliant CE Marked
CERTIFICATIONS	IEC 60269-1 IEC 60269-2 DIN 43620

AMPERAGE RATING	250 A
FITTED WITH:	Metal gripping lugs
FUSE SIZE	NH2
CURRENT TYPE	AC
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
RATED SWITCHING CAPACITY	120 kA
RATED VOLTAGE AC	690 V
CLASS	Class gG/gL
FUSE TYPE	Square body with knife blade contact
ACCESSORY/SPARE PART TYPE	SDL-2 Solid link FEH- Fuse extraction handle SD12-SK Shroud kit SD12-PB 2-phase barriers and 2 ganging links TD2-IP20 Triple pole protection kit
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	23 W
CONNECTION	Blade end
CONSTRUCTION	NH2
CONSTRUCTION SIZE	NH2
FUSE SHAPE	Square body Knife blade contacts
VOLTAGE TYPE	AC
SUITABLE FOR	SD2-D Single pole NH Fuse base Microswitch 170H0235 Microswitch 170H0236 EBH Size 00 to 4 Horizontal fuse switch-disconnectors TD2-D Triple pole NH Fuse

	base
MATERIAL	Ceramic body
PACKAGING TYPE	Standard
QUANTITY	3
VOLTAGE RATING	690 V
TYPE	Fuse
SPECIAL FEATURES	Live gripping lug
APPLICATION	• industrial • Utilities, Solar, Wind
RATED SWITCHING CAPACITY AC	120 kA

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: