

Eaton 250NHM2B

Fuse-link, low voltage, 250 A, AC 500 V, NH2, aM, IEC, dual indicator

PRODUCT NAME	Eaton Bussmann series low voltage NH Fuse
CATALOG NUMBER	250NHM2B
PRODUCT LENGTH/DEPTH	150 mm
PRODUCT HEIGHT	71 mm
PRODUCT WIDTH	54 mm
PRODUCT WEIGHT	659 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269-1 IEC 60269-2 DIN 43620

AMPERAGE RATING	250 A
FITTED WITH:	Metal gripping lugs
FUSE SIZE	NH2
CURRENT TYPE	AC
BREAKING CAPACITY	120 kA
RATED SWITCHING CAPACITY	120 kA
RATED VOLTAGE AC	500 V
CLASS	Class aM
FUSE TYPE	Square body with knife blade contact
ACCESSORY/SPARE PART TYPE	SDL-2 Solid link FEH- Fuse extraction handle SD12-SK Shroud kit SD12-PB 2-phase barriers and 2 ganging links TD2-IP20 Triple pole protection kit
UTILIZATION CATEGORY	aM (switchgear protection)
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	17 W
CONNECTION	Blade end
CONSTRUCTION	NH2
CONSTRUCTION SIZE	NH2
FUSE SHAPE	Square body Knife blade contacts
VOLTAGE TYPE	AC
SUITABLE FOR	SD2-D Single pole NH Fuse base Microswitch 170H0235 Microswitch 170H0236 EBH Size 00 to 4 Horizontal fuse switch-disconnectors TD2-D Triple pole NH Fuse base
MATERIAL	Ceramic body
QUANTITY	3
VOLTAGE RATING	500 V
TYPE	Fuse

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-nh-fuse-declaration-of-conformity-uk250970en.pdf](#)

APPLICATION	industrial
RATED SWITCHING CAPACITY AC	120 kA

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

