



Eaton 25NHG01B

Eaton Bussmann series low voltage NH Fuse, Live gripping lug, 500V, 25A, 120 kAIC, Combination fuse status indicator, fuse, Blade end connection, Class C gL/gG, Square-body with knife blade contact, Ceramic body

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage NH Fuse
CATALOG NUMBER	25NHG01B
UPC	051712625920
PRODUCT LENGTH/DEPTH	135 mm
PRODUCT HEIGHT	57.8 mm
PRODUCT WIDTH	29.55 mm
PRODUCT WEIGHT	0.261 kg
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269-1 IEC 60269-2 DIN 43620



Powering Business Worldwide

0000

AMPERAGE RATING	25 A
FITTED WITH:	Metal gripping lugs
FUSE SIZE	NH0
CURRENT TYPE	AC
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
RATED SWITCHING CAPACITY	120 kA
RATED VOLTAGE AC	500 V
CLASS	Class gG/gL
FUSE TYPE	Square body with knife blade contact
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	Blade end
CONSTRUCTION	NH01
CONSTRUCTION SIZE	NH01
FUSE SHAPE	Square body Knife blade contacts
VOLTAGE TYPE	AC
SUITABLE FOR	EBF Vertical fuse rail EBV Vertical fuse switch-disconnectors
MATERIAL	Ceramic body
QUANTITY	3
VOLTAGE RATING	500 V
TYPE	fuse
SPECIAL FEATURES	Live gripping lug
APPLICATION	• industrial • Utilities, Solar, Wind

□□

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-nh-fuse-declaration-of-conformity-uk250953en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

