



## Eaton 25TB40

Expulsion fuse-link, medium voltage, 40 A, AC 25 kV, 660 mm, ANSI, T slow, style B termination

□□□□

|                                 |                                                           |
|---------------------------------|-----------------------------------------------------------|
| <b>PRODUCT NAME</b>             | Eaton Bussmann series<br>medium voltage expulsion<br>fuse |
| <b>CATALOG NUMBER</b>           | 25TB40                                                    |
| <b>PRODUCT<br/>LENGTH/DEPTH</b> | 225 mm                                                    |
| <b>PRODUCT HEIGHT</b>           | 76 mm                                                     |
| <b>PRODUCT WIDTH</b>            | 106 mm                                                    |
| <b>PRODUCT WEIGHT</b>           | 42.04 g                                                   |
| <b>CERTIFICATIONS</b>           | ANSI/IEEE Std C37.42                                      |

| Eaton                       |                                                                                    |
|-----------------------------|------------------------------------------------------------------------------------|
| AMPERAGE RATING             | 40 A                                                                               |
| CURRENT CHARACTERISTIC TYPE | Type T - Complies with ANSI C 37-42 requirements for slow acting T characteristics |
| RATED FREQUENCY - MAX       | 60 Hz                                                                              |
| RATED FREQUENCY - MIN       | 50 Hz                                                                              |
| RELEASE CHARACTERISTIC      | T                                                                                  |
| STANDARD                    | ANSI                                                                               |
| TYPE OF TERMINATION         | Fixed buttonhead                                                                   |
| VOLTAGE TYPE                | AC                                                                                 |
| COLOR                       | Green                                                                              |
| INTERRUPT RATING            | 8 kAIC                                                                             |
| CONSTRUCTION SIZE           | 660 mm                                                                             |
| VOLTAGE RATING              | 25 kV                                                                              |
| TYPE                        | Medium Voltage Expulsion Fuse Link                                                 |
| APPLICATION                 | Primary side transformer protection, feeder protection, capacitor bank protection  |

|  |
|--|
|  |
|  |
|  |
|  |