



Eaton 25TB50

Expulsion fuse-link, medium voltage, 50 A, AC 25 kV, 660 mm, ANSI, T slow, style B termination

□□□□

PRODUCT NAME	Eaton Bussmann series medium voltage expulsion fuse
CATALOG NUMBER	25TB50
PRODUCT LENGTH/DEPTH	225 mm
PRODUCT HEIGHT	76 mm
PRODUCT WIDTH	106 mm
PRODUCT WEIGHT	42.04 g
CERTIFICATIONS	ANSI/IEEE Std C37.42

Eaton	
AMPERAGE RATING	50 A
CURRENT CHARACTERISTIC TYPE	Type T - Complies with ANSI C 37-42 requirements for slow acting T characteristics
RATED FREQUENCY - MAX	60 Hz
RATED FREQUENCY - MIN	50 Hz
RELEASE CHARACTERISTIC	T
STANDARD	ANSI
TYPE OF TERMINATION	Fixed buttonhead
VOLTAGE TYPE	AC
COLOR	Green
INTERRUPT RATING	8 kAIC
CONSTRUCTION SIZE	660 mm
VOLTAGE RATING	25 kV
TYPE	Medium Voltage Expulsion Fuse Link
APPLICATION	Primary side transformer protection, feeder protection, capacitor bank protection
