



Eaton 25TB8

Expulsion fuse-link, medium voltage, 8 A, AC
25 kV, 660 mm, ANSI, T slow

□□□□

PRODUCT NAME	Eaton Bussmann series medium voltage expulsion fuse
CATALOG NUMBER	25TB8
PRODUCT LENGTH/DEPTH	660 mm
PRODUCT HEIGHT	19 mm
PRODUCT WIDTH	19 mm
PRODUCT WEIGHT	20.2 g
CERTIFICATIONS	ANSI/IEEE Std C37.42

Eaton	
AMPERAGE RATING	8 A
CURRENT CHARACTERISTIC TYPE	Type T - Complies with ANSI C 37-42 requirements for slow acting T characteristics
RATED FREQUENCY - MAX	60 Hz
RATED FREQUENCY - MIN	50 Hz
RELEASE CHARACTERISTIC	T
STANDARD	ANSI
TYPE OF TERMINATION	Fixed buttonhead
VOLTAGE TYPE	AC
COLOR	Green
INTERRUPT RATING	8 kAIC
CONSTRUCTION SIZE	660 mm
VOLTAGE RATING	25 kV
TYPE	Medium Voltage Expulsion Fuse Link
APPLICATION	Primary side transformer protection, feeder protection, capacitor bank protection

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton

Follow us on social media to get the latest product and support information.

