



Eaton 25TB80

Eaton Bussmann series medium voltage expulsion fuse, 25KV 80AMP LINK, Type T - Complies with ANSI C 37-42 requirements for slow acting T characteristics, No removable buttonhead, Green, 660 mm, 25 kV

□□□□

PRODUCT NAME	Eaton Bussmann series medium voltage expulsion fuse
CATALOG NUMBER	25TB80
PRODUCT LENGTH/DEPTH	19 mm
PRODUCT HEIGHT	660 mm
PRODUCT WIDTH	19 mm
PRODUCT WEIGHT	36.4 g
CERTIFICATIONS	ANSI/IEEE Std C37.42

Eaton		Eaton	
AMPERAGE RATING	80 A		
CURRENT CHARACTERISTIC TYPE	Type T - Complies with ANSI C 37-42 requirements for slow acting T characteristics		
RELEASE CHARACTERISTIC	T		
STANDARD	ANSI		
TYPE OF TERMINATION	No removable buttonhead		
COLOR	Green		
CONSTRUCTION SIZE	660 mm		
VOLTAGE RATING	25 kV		
TYPE	Medium Voltage Expulsion Fuse Link		
APPLICATION	Primary side transformer protection, feeder protection, capacitor bank protection		

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE: