



Eaton 262415

Eaton Distribution parts. Auxiliary contact,
for FI..., 2W, 0.5HP

□□□□

PRODUCT NAME	Eaton Distribution parts
CATALOG NUMBER	262415
PRODUCT LENGTH/DEPTH	80 mm
PRODUCT HEIGHT	75 mm
PRODUCT WIDTH	8.8 mm
PRODUCT WEIGHT	0.045 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	EN45545-2 IEC 61373

□□□□

USED WITH	Accessory for residual current circuit breaker Accessory
ACCESSORY/SPARE PART TYPE	Auxiliary contacts
ADDITIONAL EQUIPMENT REQUIRED	Other
AMBIENT OPERATING TEMPERATURE - MAX	40 °C
AMBIENT OPERATING TEMPERATURE - MIN	-5 °C
ASSEMBLY WIDTH	0.5 TE
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	2
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	0
NUMBER OF POLES AT MAIN CONTACT UNIT - MAX	2
NUMBER OF SWITCHES (FAULT SIGNAL)	0
RATED INSULATION VOLTAGE (UI)	250 VAC
VOLTAGE TYPE	AC
FUNCTIONS	Auxiliary switch
DEVICE FITTING	Earth leakage switch
TYPE	• Accessory • Accessory for residual current circuit breaker
RATED OPERATIONAL VOLTAGE (UE) - MAX	230 V
RATED SWITCH CURRENT	6 A
SUITABLE FOR CURRENT OF MAIN CONTACT UNIT - MAX	0 A
RATED OPERATIONAL CURRENT	0.5 A (110 V DC-12)

□□

MCAD MODEL

[z_nhk.stp](#)

