



Eaton 264243

Eaton Moeller® series Rapid Link Entry, flat cable, for enclosures

□□□□

PRODUCT NAME	Eaton Rapid Link Accomplishment
CATALOG NUMBER	264243
PRODUCT LENGTH/DEPTH	65 mm
PRODUCT HEIGHT	20 mm
PRODUCT WIDTH	45 mm
PRODUCT WEIGHT	0.033 kg
COMPLIANCES	CE

0000

FEATURES	Watertight Halogen free
THREAD SIZE	0
BORE DIAMETER	0 mm
FOR WALL THICKNESS - MAX	0 mm
FOR WALL THICKNESS - MIN	0 mm
NUMBER OF CABLES - MAX	1
NUMBER OF CABLES - MIN	1
OPERATING TEMPERATURE - MAX	55 °C
OPERATING TEMPERATURE - MIN	-10 °C
SUITABLE FOR CABLE DIAMETER - MAX	0 mm
SUITABLE FOR CABLE DIAMETER - MIN	0 mm
PRODUCT CATEGORY	Power supply
THREAD SIZE (PG)	0
CABLE ENTRY TYPE	Long-slot
COLOR	Black
DEGREE OF PROTECTION	IP65
SURFACE PROTECTION	Untreated
MATERIAL QUALITY	Polyvinyl chloride (PVC)
MATERIAL	Plastic
MODEL	Other
FUNCTIONS	For bushing for flat cable in distributor module or control cabinet

00

DECLARATIONS OF CONFORMITY	eaton-accessory-declaration-of-conformity-uk251318en.pdf
0000	eaton-rapid-link-5-brochure-br040014en-en-us.pdf
00	eaton-bus-adapter-knockout-rapidlink-accomplishment-3d-drawing.eps

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

