

## Eaton 275453

Eaton xEnergy Basic LV systems Low voltage switchgear. Connection terminal f. 35mm<sup>2</sup>

PRODUCT NAME	Eaton xEnergy Basic other accessory
CATALOG NUMBER	275453
PRODUCT LENGTH/DEPTH	25 mm
PRODUCT HEIGHT	20 mm
PRODUCT WIDTH	15 mm
PRODUCT WEIGHT	0.02 kg
COMPLIANCES	RoHS conform

USED WITH	Expansion terminal Accessory consideration BF flat distribution board
TYPE	<ul style="list-style-type: none"> <li>• Additional equipment</li> <li>• BF flat distribution board</li> </ul>
ACCESSORY/SPARE PART TYPE	General
NOMINAL CURRENT	63 A
NUMBER OF CONNECTIONS (LESS THAN 6 MM SQUARED)	0
NUMBER OF CONNECTIONS (LESS THAN AWG 6)	0
NUMBER OF CONNECTIONS (GREATER THAN 25 MM SQUARED)	1
NUMBER OF CONNECTIONS (GREATER THAN 250 KCMIL)	0
NUMBER OF CONNECTIONS (10 MM SQUARED)	0
NUMBER OF CONNECTIONS (16 MM SQUARED)	0
NUMBER OF CONNECTIONS (25 MM SQUARED)	0
NUMBER OF CONNECTIONS (250 KCMIL)	0
NUMBER OF CONNECTIONS (AWG 2)	0
NUMBER OF CONNECTIONS (AWG 4)	0
NUMBER OF CONNECTIONS (AWG 4/0)	0
NUMBER OF CONNECTIONS (AWG 6)	0
NUMBER OF CONNECTIONS (TOTAL)	1
NUMBER OF POLES	Single-pole
CONNECTION TYPE	Clamp

DECLARATIONS OF CONFORMITY	<a href="#">DA-DC-03 KLA</a>
----------------------------	------------------------------

	Screwing
<b>HOUSING MATERIAL</b>	Brass
<b>MOUNTING METHOD</b>	Floor standing distribution board Flush mounting Screw Surface mounting
<b>SUITABLE FOR</b>	Fine strand conductors Solid conductors Stranded conductors
<b>FUNCTIONS</b>	Additional equipment
<b>TERMINAL CAPACITY</b>	35 mm <sup>2</sup>
<b>CONDUCTOR CROSS SECTION, INPUT - MIN</b>	16 mm <sup>2</sup>
<b>CONDUCTOR CROSS SECTION, OUTPUT AWG - MIN</b>	0 mm <sup>2</sup>
<b>CONDUCTOR CROSS SECTION, INPUT - MAX</b>	35 mm <sup>2</sup>
<b>CONDUCTOR CROSS SECTION, INPUT AWG - MAX</b>	0 mm <sup>2</sup>
<b>NUMBER OF INPUTS</b>	1
<b>CONDUCTOR CROSS SECTION, INPUT AWG - MIN</b>	0 mm <sup>2</sup>
<b>NUMBER OF OUTPUTS</b>	1
<b>CONDUCTOR CROSS SECTION, OUTPUT - MAX</b>	10 mm <sup>2</sup>
<b>CONDUCTOR CROSS SECTION, OUTPUT AWG - MAX</b>	0 mm <sup>2</sup>
<b>CONDUCTOR CROSS SECTION, OUTPUT - MIN</b>	10 mm <sup>2</sup>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com  
© 2025

Follow us on social media to get the latest product and support information.

