



□□□□□

Eaton 278518

Eaton Distribution parts. Shunt release, up to 63A, 12-110V, 1HP

□□□□

PRODUCT NAME	Eaton Distribution parts
CATALOG NUMBER	278518
PRODUCT LENGTH/DEPTH	80 mm
PRODUCT HEIGHT	75.5 mm
PRODUCT WIDTH	17.7 mm
PRODUCT WEIGHT	0.087 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	EN45545-2 IEC 61373
CATALOG NOTES	110VAC)

□□□□	
USED WITH	Accessory for miniature circuit breaker Accessory
ACCESSORY/SPARE PART TYPE	Shunt release
DEGREE OF PROTECTION	IP40
FRAME	Standard front dimension: 45 mm
FREQUENCY RATING	50 Hz / 60 Hz
MOUNTING METHOD	Top-hat rail IEC/EN 60715
ADDITIONAL EQUIPMENT REQUIRED	Shunt release (for power circuit breaker)
TERMINAL PROTECTION	Protection against electric shock to IEC 536
TERMINAL TYPE	Twin-purpose terminals
VOLTAGE RANGE	12 V AC - 110 V AC
AMBIENT OPERATING TEMPERATURE - MAX	40 °C
AMBIENT OPERATING TEMPERATURE - MIN	-5 °C
ASSEMBLY WIDTH	1 TE
ENCLOSURE WIDTH	80 mm
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	1
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	1
NUMBER OF POLES AT MAIN CONTACT UNIT - MAX	1
NUMBER OF SWITCHES (FAULT SIGNAL)	0
VOLTAGE TYPE	AC
FUNCTIONS	Shunt release (for power circuit breaker)
DEVICE FITTING	Miniature circuit breaker (MCB)
TYPE	• Accessory • Accessory for miniature circuit breaker
MOUNTING WIDTH	17.5 mm (1 space unit)

□□	
MCAD MODEL	faz_xaa.stp
□□□□□	IL1777

RATED OPERATIONAL VOLTAGE (UE) - MAX	110 V
TERMINAL CAPACITY (CABLE)	1 mm² - 2.5 mm²
TERMINAL CAPACITY (SOLID WIRE)	1 mm² - 2.5 mm²
