

Eaton 286052

Eaton Distribution parts. Auxiliary contact, for PLS, postal Code, PKNM, ZP-A40...-ASA...IHK...WHK, Z-MS, 1N/O+1N/C, 0.5HP

PRODUCT NAME	Eaton Distribution parts
CATALOG NUMBER	286052
PRODUCT LENGTH/DEPTH	80 mm
PRODUCT HEIGHT	75 mm
PRODUCT WIDTH	8.8 mm
PRODUCT WEIGHT	0.043 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	EN45545-2 IEC 61373

USED WITH	Auxiliary contacts
	Accessory for combined residual current/power circuit breaker
	Accessory for miniature circuit breaker
	Accessory
ACCESSORY/SPARE PART TYPE	Auxiliary contacts
MOUNTING METHOD	For fitting on left to: LS, FI/LS
ADDITIONAL EQUIPMENT REQUIRED	Auxiliary switch
AMBIENT OPERATING TEMPERATURE - MAX	55 °C
AMBIENT OPERATING TEMPERATURE - MIN	-5 °C
ASSEMBLY WIDTH	0.5 TE
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	1
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	1
NUMBER OF POLES AT MAIN CONTACT UNIT - MAX	2
NUMBER OF SWITCHES (FAULT SIGNAL)	0
VOLTAGE TYPE	AC
FUNCTIONS	Auxiliary switch
DEVICE FITTING	Universal
TYPE	<ul style="list-style-type: none"> • Accessory • Accessory for combined residual current/power circuit breaker • Accessory for miniature circuit breaker
APPLICATION	Switchgear for industrial and advanced commercial applications

DECLARATIONS OF CONFORMITY

[DA-DC-03 ZP-IHK](#)

RATED OPERATIONAL VOLTAGE (UE) - MAX	230 V
RATED SWITCH CURRENT	3 A
SUITABLE FOR CURRENT OF MAIN CONTACT UNIT - MAX	6 A

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

