

## Eaton 286053

Eaton Distribution parts. Auxiliary contact, for PLS, postal Code, PKNM, ZP-A40...-ASA...IHK...WHK, Z-MS, 1W, 0.5HP

<b>PRODUCT NAME</b>	Eaton Distribution parts
<b>CATALOG NUMBER</b>	286053
<b>PRODUCT LENGTH/DEPTH</b>	80 mm
<b>PRODUCT HEIGHT</b>	75 mm
<b>PRODUCT WIDTH</b>	8.8 mm
<b>PRODUCT WEIGHT</b>	0.038 kg
<b>COMPLIANCES</b>	RoHS conform
<b>CERTIFICATIONS</b>	EN45545-2 IEC 61373

USED WITH	Trigger signal contact
	Accessory
	Accessory for miniature circuit breaker
	Accessory for combined residual current/power circuit breaker
ACCESSORY/SPARE PART TYPE	Auxiliary contacts
MOUNTING METHOD	For fitting on left to: LS, FI/LS
ADDITIONAL EQUIPMENT REQUIRED	Auxiliary switch
AMBIENT OPERATING TEMPERATURE - MAX	55 °C
AMBIENT OPERATING TEMPERATURE - MIN	-5 °C
ASSEMBLY WIDTH	0.5 TE
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	1
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	0
NUMBER OF POLES AT MAIN CONTACT UNIT - MAX	1
NUMBER OF SWITCHES (FAULT SIGNAL)	0
VOLTAGE TYPE	AC
FUNCTIONS	Auxiliary switch
DEVICE FITTING	Universal
TYPE	<ul style="list-style-type: none"> <li>• Accessory</li> <li>• Accessory for combined residual current/power circuit breaker</li> <li>• Accessory for miniature circuit breaker</li> </ul>
APPLICATION	Switchgear for industrial and advanced commercial applications



<b>RATED OPERATIONAL VOLTAGE (UE) - MAX</b>	230 V
<b>RATED SWITCH CURRENT</b>	3 A
<b>SUITABLE FOR CURRENT OF MAIN CONTACT UNIT - MAX</b>	6 A

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

