



## Eaton 286704

Eaton xEnergy Basic LV systems Low voltage switchgear. Cable entry / flange plate for W=400mm, closed

□□□□

<b>PRODUCT NAME</b>	Eaton xEnergy Basic other accessory
<b>CATALOG NUMBER</b>	286704
<b>PRODUCT LENGTH/DEPTH</b>	175 mm
<b>PRODUCT HEIGHT</b>	20 mm
<b>PRODUCT WIDTH</b>	345 mm
<b>PRODUCT WEIGHT</b>	0.67 kg
<b>COMPLIANCES</b>	RoHS conform



Powering Business Worldwide

TYPE	Additional equipment
NUMBER OF CONNECTOR HOLES	0
SUITABLE FOR NOMINAL THREAD (PG) - MAX	50
SUITABLE FOR NOMINAL THREAD (PG) - MIN	10
SUITABLE FOR WIDTH	400 mm
SURFACE FINISHING	With powder coating
CABLE ENTRY TYPE	Blind
COLOR	Light gray (RAL 7035)
DEGREE OF PROTECTION	IP30 Other
SURFACE PROTECTION	Powder coating
SHAPE	Straight
MATERIAL	Sheet steel Steel
HOUSING MATERIAL	Sheet steel
MODEL	Blind
MOUNTING METHOD	Surface mounting
FUNCTIONS	Additional equipment
THREAD TYPE	None
THICKNESS	1 mm
SUITABLE FOR CABLE DIAMETER - MAX	0 mm
SUITABLE FOR CABLE DIAMETER - MIN	0 mm

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

00: