



□□□□□

Eaton 288944

Eaton Distribution parts, Fuse-link, D02, 40A,
400 V, gL/gG

□□□□

PRODUCT NAME	Eaton Distribution parts
CATALOG NUMBER	288944
PRODUCT LENGTH/DEPTH	36 mm
PRODUCT HEIGHT	16 mm
PRODUCT WIDTH	16 mm
PRODUCT WEIGHT	0.013 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	DIN VDE 0636 DIN 49522



Powering Business Worldwide

USED WITH	Fuse links Accessory Fuse material
AMPERAGE RATING	40 A
FRAME	D02
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection) gG (gL)
EQUIPMENT HEAT DISSIPATION, CURRENT- DEPENDENT	3.7 W
COLOR	Black
AMBIENT OPERATING TEMPERATURE - MAX	55 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
HEAT DISSIPATION CAPACITY	0 W
HEAT DISSIPATION PER POLE, CURRENT- DEPENDENT	0 W
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	40 A
RATED OPERATIONAL VOLTAGE (UE) - MAX	400 V
RATED UNINTERRUPTED CURRENT (IU)	40 A
STATIC HEAT DISSIPATION, NON- CURRENT-DEPENDENT	0 W
VOLTAGE RATING AT DC	220 V DC
FUNCTIONS	Accessory
FUSE CARTRIDGE	D02
VOLTAGE RATING	400 V AC

TYPE	• Accessory • Fuse links • Fuse material
SPECIAL FEATURES	• Snap-fit on DIN rail • in a plastic box in the colour of the indicator

