

Eaton 290210

Eaton Moeller® series Rapid Link Power incoming cable, flat cable, L=1.5m

PRODUCT NAME	Eaton Rapid Link Power adapter cable
CATALOG NUMBER	290210
PRODUCT LENGTH/DEPTH	1.5 m
PRODUCT HEIGHT	50 mm
PRODUCT WIDTH	240 mm
PRODUCT WEIGHT	0.429 kg
COMPLIANCES	CE

FEATURES	Connector system system-oriented
	Oil resistant (acc. EN 60811-404)
FITTED WITH:	Power plug and plug for flexible busbar junction, halogen-free, 5 x 1.5 mm ² Protective conductor
COLOR	Gray
CONNECTION 1	Other
CONNECTION 2	Other
DEGREE OF PROTECTION	Other
FUNCTIONS	For connecting the device with the 400 V AC flexible busbar junction
EURO CLASS ACIDITY (EN 13501-6)	None
EURO CLASS FLAMING DROPLETS/PARTICLES (EN 13501-6)	None
OUTER SHEATH COLOR	Gray
REACTION-TO-FIRE CLASS (EN 13501-6)	None
SPIRALIZED CABLE	No
FREQUENCY RATING - MAX	60 Hz
FREQUENCY RATING - MIN	50 Hz
NOMINAL CROSS SECTION (CONDUCTOR)	1.5 mm ²
NOMINAL CURRENT	6.6 A
NOMINAL VOLTAGE - MAX	480 V
NOMINAL VOLTAGE - MIN	480 V
NUMBER OF CORES	5
OUTER DIAMETER - APPROXIMATE	10 mm
PERMISSIBLE AMBIENT TEMPERATURE - MAX	55 °C
PERMISSIBLE AMBIENT TEMPERATURE - MIN	-10 °C
PRODUCT CATEGORY	Power supply
OUTER SHEATH MATERIAL	Other

DECLARATIONS OF CONFORMITY	DA-DC-00003950.pdf
	DA-DC-00003685.pdf
	eaton-rapid-link-5-brochure-br040014en-en-us.pdf
	eaton-powerxl-variable-frequency-drives-material-handling-brochure-br040017en-en-us.pdf
	eaton-bus-adapter-cable-rapidlink-power-adapter-cable-3d-drawing.eps

SMOKE DEVELOPMENT CLASS (EN 13501-6)	None
CABLE ENTRY CONNECTION 1	Straight
CABLE ENTRY CONNECTION 2	Straight

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

