



□□□□□

Eaton 291470

Eaton Moeller series xPole - Busbar. EV busbars 3Ph., 6HP, 80A for PLS. CLS. PKN., PFIM, PFHM, PFNM

□□□□

PRODUCT NAME	Eaton Moeller series busbar
CATALOG NUMBER	291470
PRODUCT LENGTH/DEPTH	33 mm
PRODUCT HEIGHT	10.4 mm
PRODUCT WIDTH	103 mm
PRODUCT WEIGHT	0.052 kg
COMPLIANCES	RoHS conform

□□□□

USED WITH	Busbar EVG
TYPE	• Busbar • EVG
FEATURES	Insulated
ACCESSORY/SPARE PART TYPE	Busbar for miniature circuit breaker Busbar for combined residual current/power circuit breaker Busbar for residual current circuit breakers
ELECTRIC CONNECTION TYPE	Fork
RATED SURGE VOLTAGE	4 kV
RATED UNINTERRUPTED CURRENT (IU)	80 A
SUITABLE FOR NUMBER OF DEVICES	2
NUMBER OF POLES	Three-pole
COLOR	Other
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	0 kA
CROSS SECTION	16 mm ²
NUMBER OF MODULAR SPACINGS	6
NUMBER OF PHASES	3
PITCH DIMENSIONS	0 mm
RATED OPERATIONAL VOLTAGE (UE) - MAX	415 V
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	25 kA
FUNCTIONS	Busbar
SUITABLE FOR	2 devices

□□

[eaton-mcb-busbar-dimensions-007.eps](#)

□□

[eaton-busbar-3d-drawing.jpg](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

