



Eaton 291484

Eaton Moeller series xPole - Busbar. EV busbars 2Ph., 12HP, for auxiliary contact unit, 16

□□□□

PRODUCT NAME	Eaton Moeller series busbar
CATALOG NUMBER	291484
PRODUCT LENGTH/DEPTH	33 mm
PRODUCT HEIGHT	7.8 mm
PRODUCT WIDTH	210 mm
PRODUCT WEIGHT	0.09 kg
COMPLIANCES	RoHS conform

USED WITH	Busbar EVG
TYPE	<ul style="list-style-type: none">• Busbar• EVG
FEATURES	Insulated
ACCESSORY/SPARE PART TYPE	Busbar for miniature circuit breaker Busbar for combined residual current/power circuit breaker Busbar for residual current circuit breakers
ELECTRIC CONNECTION TYPE	Fork
RATED SURGE VOLTAGE	4 kV
RATED UNINTERRUPTED CURRENT (IU)	80 A
SUITABLE FOR NUMBER OF DEVICES	5
NUMBER OF POLES	Two-pole
COLOR	Other
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	0 kA
CROSS SECTION	16 mm ²
NUMBER OF MODULAR SPACINGS	10
NUMBER OF PHASES	2
PITCH DIMENSIONS	0 mm
RATED OPERATIONAL VOLTAGE (UE) - MAX	415 V
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	25 kA
FUNCTIONS	Busbar
SUITABLE FOR	Devices with auxiliary switch 5 devices

□□ [eaton-busbar-3d-drawing.jpg](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

