



Eaton 3.6WDFHO125

Eaton Bussmann series medium voltage motor fuse, 25 A, 3.6 kV, 51 x 254 mm, Non Indicating

PRODUCT NAME	Eaton Bussmann series medium voltage motor fuse
CATALOG NUMBER	3.6WDFHO125
UPC	051712603102
PRODUCT LENGTH/DEPTH	254 mm
PRODUCT HEIGHT	51 mm
PRODUCT WIDTH	51 mm
PRODUCT WEIGHT	1460 g
COMPLIANCES	BS 2692-1



USED WITH	A3354710 Nickel-plated copper fuse clip
AMPERAGE RATING	25 A
FUSE INDICATOR	Non Indicating
FUSE SIZE	51 x 254 mm
BREAKING CAPACITY	50 A
INSTALLATION TECHNIQUE	Air
PERFORMANCE CAT ACCORDING TO IEC 60282-1	Back-up
PRODUCT APPLICATION	Motor protection
RATED FREQUENCY - MAX	50 Hz
RATED FREQUENCY - MIN	50 Hz
RELEASE CHARACTERISTIC	Other
STANDARD	British Standard
UTILIZATION CATEGORY	Other
VOLTAGE TYPE	AC
WITH STRIKER	Yes
CLASS	Class back-up
BARRELS	1
FUSE SHAPE	Cylindrical, offset bolted tags
WATT LOSSES	53 W
RESISTANCE	2.44 ohms
FUSE DIAMETER	51 mm
INTERRUPT RATING	50 kAIC
CONSTRUCTION SIZE	51 x 254 mm
PACKAGING TYPE	Standard
VOLTAGE RATING	3.6 kV
TYPE	fuse
APPLICATION	Motor protection
FUSE TYPE	WDFH



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

