



## Eaton 300650

Eaton Moeller series xComfort - Go wireless packages. Central dimming point package, preconfigured

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller series xComfort dimming package
<b>CATALOG NUMBER</b>	300650
<b>PRODUCT LENGTH/DEPTH</b>	73 mm
<b>PRODUCT HEIGHT</b>	75 mm
<b>PRODUCT WIDTH</b>	86 mm
<b>PRODUCT WEIGHT</b>	0.133 kg
<b>COMPLIANCES</b>	RoHS conform

## □□□□

<b>USED WITH</b>	55 mm (Universal) pushbutton
<b>FEATURES</b>	Radio frequent bidirectional
<b>BUS SYSTEM OPERATING TYPE</b>	Radio frequent xComfort
<b>ACTUATION FUNCTION</b>	Dimming
<b>BUS SYSTEM PRODUCT TYPE</b>	Packaged Units
<b>BUILT-IN INSTALLATION BOX DEPTH - MIN</b>	18 mm
<b>FREQUENCY RATING - MAX</b>	50 Hz
<b>FREQUENCY RATING - MIN</b>	50 Hz
<b>NUMBER OF GANGS (ROCKER)</b>	4
<b>OUTPUT POWER - MAX</b>	250 W
<b>OUTPUT POWER - MIN</b>	0 W
<b>RATED CONTROL SUPPLY CURRENT IS</b>	0 mA
<b>FITTED WITH:</b>	Bus connection LED indication
<b>SWITCHING POWER LED - MAX</b>	100 W
<b>VOLTAGE RATING - MAX</b>	253 V
<b>VOLTAGE RATING - MIN</b>	196 V
<b>WIDTH IN NUMBER OF MODULAR SPACINGS</b>	3
<b>POWER SUPPLY</b>	Battery Mains
<b>NUMBER OF OUTPUTS</b>	1
<b>DEGREE OF PROTECTION</b>	IP20
<b>LOAD TYPE</b>	Universal and LED retrofit
<b>MODEL</b>	Dimming actuator
<b>MOUNTING METHOD</b>	Surface mounting Flush mounting Flush mounted (plaster)
<b>SUITABLE FOR</b>	Constant current Constant voltage

## □□

[go-wireless-selection-guide-leaflet.pdf](#)

## □□□□

[eaton-xcomfort-thune-eiendom-success-story-cs083094en-en-us.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

