



## Eaton 300RC

Eaton Bussmann series high speed traction fuse, 300A, 80 kAIC, None, Fuse, Class C gL/gG

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed traction fuse
<b>CATALOG NUMBER</b>	300RC
<b>UPC</b>	051712565608
<b>PRODUCT LENGTH/DEPTH</b>	232 mm
<b>PRODUCT HEIGHT</b>	74 mm
<b>PRODUCT WIDTH</b>	74 mm
<b>PRODUCT WEIGHT</b>	1.2 kg
<b>COMPLIANCES</b>	Contact factory



Powering Business Worldwide

□□□□

<b>AMPERAGE RATING</b>	300 A
<b>BREAKING CAPACITY</b>	80 kA
<b>VOLTAGE TYPE</b>	DC
<b>UTILIZATION CATEGORY</b>	Other
<b>RELEASE CHARACTERISTIC</b>	Other
<b>FUSE INDICATOR</b>	None
<b>FREQUENCY RATING - MIN</b>	45 Hz
<b>FREQUENCY RATING - MAX</b>	62 Hz
<b>RATED SWITCHING CAPACITY</b>	80 A
<b>CLASS</b>	Class C gL/gG
<b>WATT LOSSES</b>	37 W
<b>FUSE SHAPE</b>	Center bolted tags
<b>MOUNTING DIMENSION</b>	M10
<b>CENTER-TO-CENTER DISTANCE OF CONNECTIONS</b>	196.6 mm
<b>CURRENT TYPE</b>	DC
<b>RATED VOLTAGE DC</b>	750 V
<b>COLOR</b>	None
<b>INTERRUPT RATING</b>	80 kAIC
<b>CONSTRUCTION SIZE</b>	Other
<b>MATERIAL</b>	Ceramic
<b>PACKAGING TYPE</b>	Standard
<b>VOLTAGE RATING</b>	750 V
<b>TYPE</b>	Fuse
<b>APPLICATION</b>	traction
<b>FUSE SYSTEM (ACCORDING TO IEC 60269)</b>	Other

□□

DECLARATIONS OF CONFORMITY

[eaton-high-speed-traction-fuse-declaration-of-conformity-uk250895en.pdf](#)

