

Eaton 302105

Eaton xEffect SASY 60i Enclosures Switch- & Controlgear Enclosure. Busbar support 1-pole, profile to 720mm²

PRODUCT NAME	Eaton xEffect SASY 60i busbar support
CATALOG NUMBER	302105
PRODUCT LENGTH/DEPTH	111 mm
PRODUCT HEIGHT	72 mm
PRODUCT WIDTH	24 mm
PRODUCT WEIGHT	0.13 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC/EN 61439-2

USED WITH	Double T profile System for profile busbars 60 mm system
SPECIAL FEATURES	<ul style="list-style-type: none"> • Suitable for assembly of PE or N bar • as a standalone support or for attaching to BBS-3/PR
TYPE	<ul style="list-style-type: none"> • 60 mm system • System for profile busbars
FEATURES	Self-extinguishing acc. UL 94 Halogen free
CREEPAGE RESISTANCE	CTI 600
CURRENT RATING - MAX	1600 A
VOLTAGE RATING	690 V
BUSBAR DISTANCE	60 mm
RATED INSULATION VOLTAGE (UI)	1000 V
NUMBER OF POLES	Single-pole
COLOR	Light gray (RAL 7035)
DISTANCE BETWEEN BUSBAR CENTERS	60 mm
MOUNTING POSITION	Vertical, horizontal
CURRENT RATING (PEAK WITHSTAND)	40 kA (720 mm ²) 40 kA (500 mm ²)
FUNCTIONS	Busbar support Double T profile busbar carrier
TEMPERATURE RESISTANCE	Up to 125 °C
DISTANCE BETWEEN BUSBAR SUPPORTS	500 mm
RATED OPERATION CURRENT (IE)	1600 A
SUITABLE FOR	Single-pole
FLAMMABILITY CHARACTERISTICS (UL)	Self-extinguishing (UL 94)
MATERIAL	Thermoplast, silicon free, chlorine free



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

