



Eaton 302409

Eaton Metering Board BI-Skap/TKS LV systems Final Distribution Boards. TKS Norway meter cabinet for outdoor installation, NEK-399, incl. package for 230 V TT/IT grounding system, RAL7035



PRODUCT NAME	Eaton Metering Board BI-Skap/TKS LV systems Final Distribution Boards
CATALOG NUMBER	302409
PRODUCT LENGTH/DEPTH	265 mm
PRODUCT HEIGHT	1600 mm
PRODUCT WIDTH	415 mm
PRODUCT WEIGHT	35.5 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC/EN 61439-3



Powering Business Worldwide

SPECIAL FEATURES	<ul style="list-style-type: none"> • Pre-wired cabinet • Supplied with fuse switch disconnecter, Isolator, Surge protection device • With cable duct
-------------------------	---

TYPE	<ul style="list-style-type: none"> • TKS Norway • Compact
FITTED WITH:	Mounting plate
DEGREE OF PROTECTION	IP55 IK10
NUMBER OF FIELDS	1
NUMBER OF METER CABINETS	1
NUMBER OF TSG-PANELS	0
APPLICATION	<ul style="list-style-type: none"> • Basic device • Outdoor
RAL-NUMBER	7035
COVER/DOOR TYPE	Door with 3-point-locking system and rotary-handle
VOLTAGE RATING	230 V AC
BUILT-IN DEPTH	220 mm
BUILT-IN HEIGHT	1600 mm
BUILT-IN WIDTH	415 mm
NUMBER OF DISTRIBUTOR ROWS	2
COLOR	Grey
MATERIAL	Steel plate Aluminum, powder-coated Other
MOUNTING METHOD	Surface mounted (plaster)
NUMBER OF ROWS	2
FREQUENCY RATING OF CONTACTS	50 Hz
LOWER CONNECTION SPACE	With clamps
MODEL	1-story
MODULE RACK TYPE	DIN rail
NUMBER OF MODULE SPACE UNITS PER ROW	12
PROTECTION CLASS	I (earthed)

