

Eaton 315NHM3B-690

Eaton Fuse-link, LV, 315 A, AC 690 V, NH3, aM, IEC, dual indicator, live gripping lugs

PRODUCT NAME	Eaton Bussmann series low voltage NH Fuse
CATALOG NUMBER	315NHM3B-690
PRODUCT LENGTH/DEPTH	150 mm
PRODUCT HEIGHT	86 mm
PRODUCT WIDTH	72 mm
PRODUCT WEIGHT	1139.33 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269-1 IEC 60269-2 DIN 43620

AMPERAGE RATING	315 A
FITTED WITH:	Metal gripping lugs
FUSE SIZE	NH3
CURRENT TYPE	AC
BREAKING CAPACITY	120 kA
RATED SWITCHING CAPACITY	120 kA
RATED VOLTAGE AC	690 V
CLASS	Class aM
FUSE TYPE	Square body with knife blade contact
ACCESSORY/SPARE PART TYPE	SDL-3 Solid link FEH- Fuse extraction handle SD3-SK Shroud kit SD3-PB 2-phase barriers and 2 ganging links TD3-IP20 Triple pole protection kit
UTILIZATION CATEGORY	aM (switchgear protection)
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	20 W
CONNECTION	Blade end
CONSTRUCTION	NH3
CONSTRUCTION SIZE	NH3
FUSE SHAPE	Square body Knife blade contacts
VOLTAGE TYPE	AC
SUITABLE FOR	SD3-D Single pole NH Fuse base Microswitch 170H0235 EBH Size 00 to 4 Horizontal fuse switch-disconnectors TD3-D Triple pole NH Fuse base
MATERIAL	Ceramic body
QUANTITY	3
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	industrial



**RATED SWITCHING
CAPACITY AC**

120 kA

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

