



□□□□□

Eaton 316431

Eaton AOR/AOC Clogging Indicator,
AOR.2,5.P.-, Nitrile, 3200 psi (220 Bar), Visual

□□□□

PRODUCT NAME	Eaton AOR/AOC Clogging Indicator
CATALOG NUMBER	316431
PRODUCT LENGTH/DEPTH	30 mm
PRODUCT HEIGHT	75 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	0.081 kg
COMPLIANCES	G Threads per ISO 228

0000	
CONNECTION TYPE	G 1/2" threaded
FILTER TYPE	Clogging indicator
MATERIAL	Aluminum
APPLICATION	Wide range of clogging indicators for hydraulic and lubrication systems
SPECIFICATION	Standard
CODE STAMP	None
INDICATOR TYPE	Visual
SEALING MATERIAL	Nitrile
OPERATING TEMPERATURE - MAX	80 °C
OPERATING TEMPERATURE - MIN	-10 °C
OPERATING PRESSURE - MAX	3200 psi (220 Bar)

00

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

