

Eaton 355NHG1B

Eaton Bussmann series low voltage NH Fuse, 440V, 355A, 120 kAIC, Combination fuse status indicator, fuse, Class C gL/gG

PRODUCT NAME	Eaton Bussmann series low voltage NH Fuse
CATALOG NUMBER	355NHG1B
UPC	051712233149
PRODUCT LENGTH/DEPTH	135 mm
PRODUCT HEIGHT	63 mm
PRODUCT WIDTH	40 mm
PRODUCT WEIGHT	407.3333333 g
COMPLIANCES	RoHS Compliant CE Marked
CERTIFICATIONS	IEC 60269-1 IEC 60269-2 DIN 43620

AMPERAGE RATING	355 A
FITTED WITH:	Metal gripping lugs
FUSE SIZE	NH1
CURRENT TYPE	AC
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
RATED SWITCHING CAPACITY	120 kA
RATED VOLTAGE AC	440 V
CLASS	Class gG/gL
FUSE TYPE	Square body with knife blade contact
ACCESSORY/SPARE PART TYPE	SDL-1 Solid link FEH- Fuse extraction handle SD12-SK Shroud kit SD00-PB 2-phase barriers TD1-IP20 Triple pole protection kit
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	32 W
CONNECTION	Blade end
CONSTRUCTION	NH1
CONSTRUCTION SIZE	NH1
FUSE SHAPE	Knife blade contacts Square body
VOLTAGE TYPE	AC
SUITABLE FOR	SD1-D Single pole NH Fuse base Microswitch 170H0236 EBH Size 00 to 4 Horizontal fuse switch-disconnectors TD1-D Triple pole NH Fuse base

MATERIAL	Ceramic body
PACKAGING TYPE	Standard
QUANTITY	3
VOLTAGE RATING	440 V
TYPE	Fuse
APPLICATION	• industrial • Utilities, Solar, Wind
RATED SWITCHING CAPACITY AC	120 kA

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

