



Eaton 35KC36

Eaton Bussmann series Fuse-link, High Speed, 35 A, DC 750 V, 28 x 138 mm, gL/gG, IEC

□□□□

PRODUCT NAME	Eaton Bussmann series high speed traction fuse
CATALOG NUMBER	35KC36
UPC	051712834216
PRODUCT LENGTH/DEPTH	138 mm
PRODUCT HEIGHT	28 mm
PRODUCT WIDTH	27 mm
PRODUCT WEIGHT	154.7 g
COMPLIANCES	CE RoHS
CERTIFICATIONS	IEC

□□□□

AMPERAGE RATING	35 A
BREAKING CAPACITY	50 kA
WITH STRIKER	No
VOLTAGE TYPE	DC
UTILIZATION CATEGORY	gG (cable protection/equipment protection)
RELEASE CHARACTERISTIC	Other
FUSE INDICATOR	None
FREQUENCY RATING - MIN	45 Hz
FREQUENCY RATING - MAX	62 Hz
FUSE SIZE	27 x 138 mm
CLASS	Class gG
CLEARING (I ₂ T)	4300 at 750 Vdc
WATT LOSSES	6 W
FUSE SHAPE	Cylindrical, center bolted tags
PRE ARC (I ₂ T)	1300
MOUNTING DIMENSION	M5
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	122.7 mm
CURRENT TYPE	DC
RATED VOLTAGE DC	750 V
COLOR	None
INTERRUPT RATING	50 kA at 750 Vdc
CONSTRUCTION SIZE	Other
MATERIAL	Ceramic
PACKAGING TYPE	Standard
VOLTAGE RATING	750 V
FUSE TYPE	KC36
TYPE	Fuse
APPLICATION	traction
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□

DECLARATIONS OF CONFORMITY

[eaton-high-speed-traction-fuse-declaration-of-conformity-uk250918en.pdf](#)

