

Eaton 35LET

Eaton Bussmann series high speed British standard fuse, 35A, 280 VAC/150 VDC (UL), Class aR, 200 kA RMS Sym., Breaking capacity 200 kA RMS Sym., 50 kA DC at 150 VDC

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	35LET
UPC	051712834223
PRODUCT LENGTH/DEPTH	55 mm
PRODUCT HEIGHT	18 mm
PRODUCT WIDTH	18 mm
PRODUCT WEIGHT	31.3 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized Designed and tested to BS88 part 4 IEC 60269-4

AMPERAGE RATING	35 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
RATED SWITCHING CAPACITY	200 kA
RATED VOLTAGE AC	280 V
RATED VOLTAGE DC	150 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	41.5 mm
MOUNTING DIMENSION	M6
CURRENT TYPE	AC
CLASS	Class aR
CLEARING (I2T)	600
WATT LOSSES	5 W
FUSE SHAPE	Offset bolted tags
PRE ARC (I2T)	35
COLOR	None
INTERRUPT RATING	200 kA RMS Sym, 50 kA DC at 150 Vdc
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Stud
PACKAGING TYPE	Standard
VOLTAGE RATING	280 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	LET
SUITABLE FOR	TI500 Fuse indicator MAI Microswitch/adaptor MBI Microswitch/adaptor
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

DECLARATIONS OF CONFORMITY	DA-DC-00004682
	DA-DC-00004685

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

