

## Eaton 35NHG00BWP

Fuse-link, LV, 35 A, AC 500 V, NH00, gL/gG,  
IEC, dual indicator, live gripping lugs,  
weather resistant

<b>PRODUCT NAME</b>	Eaton Bussmann series low voltage NH Fuse
<b>CATALOG NUMBER</b>	35NHG00BWP
<b>PRODUCT LENGTH/DEPTH</b>	79 mm
<b>PRODUCT HEIGHT</b>	58 mm
<b>PRODUCT WIDTH</b>	30 mm
<b>PRODUCT WEIGHT</b>	200 g
<b>COMPLIANCES</b>	CE CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	IEC 60269-1 IEC 60269-2 DIN 43620

<b>AMPERAGE RATING</b>	35 A
<b>FITTED WITH:</b>	Metal gripping lugs
<b>FUSE SIZE</b>	NH00
<b>CURRENT TYPE</b>	AC
<b>BREAKING CAPACITY</b>	120 kA
<b>FREQUENCY RATING - MAX</b>	62 Hz
<b>FREQUENCY RATING - MIN</b>	45 Hz
<b>RATED SWITCHING CAPACITY</b>	120 kA
<b>RATED VOLTAGE AC</b>	500 V
<b>CLASS</b>	Class gG/gL
<b>FUSE TYPE</b>	Square body with knife blade contact
<b>ACCESSORY/SPARE PART TYPE</b>	FEH- Fuse extraction handle
<b>UTILIZATION CATEGORY</b>	gL/gG (cable protection/equipment protection)
<b>INTERRUPT RATING</b>	120 kAIC
<b>FUSE INDICATOR</b>	Combination fuse status indicator
<b>INSULATED METAL GRIPPING LUGS (IMGL)</b>	No
<b>WATT LOSSES</b>	4 W
<b>CONNECTION</b>	Blade end
<b>CONSTRUCTION</b>	NH00
<b>CONSTRUCTION SIZE</b>	NH00
<b>FUSE SHAPE</b>	Knife blade contacts Square body
<b>VOLTAGE TYPE</b>	AC
<b>SUITABLE FOR</b>	SD00-D Single pole NH Fuse base Microswitch 170H0236 EBH Size 00 to 4 Horizontal fuse switch-disconnectors TD00-D Triple pole NH Fuse base
<b>MATERIAL</b>	Ceramic body
<b>PACKAGING TYPE</b>	Standard
<b>QUANTITY</b>	3
<b>VOLTAGE RATING</b>	500 V



<b>TYPE</b>	Fuse
<b>SPECIAL FEATURES</b>	Weather resistant
<b>APPLICATION</b>	industrial
<b>RATED SWITCHING CAPACITY AC</b>	120 kA

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

