



Eaton 36ADIH3616

Eaton Bussmann series Air fuse-link,
medium voltage, 16 A, AC 36 kV, 50.8 x
565mm, back-up, BS, with striker

□□□□

PRODUCT NAME	Eaton Bussmann series medium voltage BS air fuse
CATALOG NUMBER	36ADIH3616
PRODUCT LENGTH/DEPTH	565 mm
PRODUCT HEIGHT	50.8 mm
PRODUCT WIDTH	50.8 mm
PRODUCT WEIGHT	0.001 g
COMPLIANCES	CE

AMPERAGE RATING	16 A
FUSE INDICATOR	With Striker
FUSE SIZE	50.8 x 565 mm
BREAKING CAPACITY	16 kA
INSTALLATION TECHNIQUE	Air
PERFORMANCE CAT ACCORDING TO IEC 60282-1	Back-up
PRODUCT APPLICATION	Primary side transformer protection
RATED FREQUENCY - MAX	50 Hz
RATED FREQUENCY - MIN	50 Hz
RELEASE CHARACTERISTIC	Other
STANDARD	British Standard
UTILIZATION CATEGORY	Other
VOLTAGE TYPE	AC
WITH STRIKER	Yes
CLASS	Class back-up
FUSE SHAPE	Cylindrical
FUSE DIAMETER	51 mm
INTERRUPT RATING	16 kAIC
CONSTRUCTION SIZE	50.8 x 565 mm
MOUNTING METHOD	Clip-in
VOLTAGE RATING	36 kV
TYPE	Fuse

APPLICATION	• protection of primary side transformers • used in fuse switch combination units, fuse bases and fuse switches
-------------	---

FUSE TYPE	ADIH
-----------	------

