

Eaton 36ADIHA16

Eaton Bussmann series medium voltage BS air fuse, 16 A, 36 kV, 16 kA, 50.8 x 565 , With Striker

PRODUCT NAME	Eaton Bussmann series medium voltage BS air fuse
CATALOG NUMBER	36ADIHA16
UPC	051712558471
PRODUCT LENGTH/DEPTH	565 mm
PRODUCT HEIGHT	50.8 mm
PRODUCT WIDTH	50.8 mm
PRODUCT WEIGHT	3000 g
COMPLIANCES	BS 2692-1

USED WITH	A3354710 Fuse clip
AMPERAGE RATING	16 A
FUSE INDICATOR	With Striker
FUSE SIZE	50.8 x 565 mm
BREAKING CAPACITY	16 kA
INSTALLATION TECHNIQUE	Air
PERFORMANCE CAT ACCORDING TO IEC 60282-1	Back-up
PRODUCT APPLICATION	Primary side transformer protection
RATED FREQUENCY - MAX	50 Hz
RATED FREQUENCY - MIN	50 Hz
RELEASE CHARACTERISTIC	Other
STANDARD	British Standard
UTILIZATION CATEGORY	Other
VOLTAGE TYPE	AC
WITH STRIKER	Yes
CLASS	Class back-up
FUSE SHAPE	Cylindrical
PRE ARC (I ² T)	1.1 x 10 ²
RESISTANCE	190 ohms
FUSE DIAMETER	51 mm
INTERRUPT RATING	16 kAIC
CONSTRUCTION SIZE	51 x 565 mm
MOUNTING METHOD	Clip-in
VOLTAGE RATING	36 kV
TYPE	Fuse
APPLICATION	<ul style="list-style-type: none"> • protection of primary side transformers • used in fuse switch combination units, fuse bases and fuse switches
FUSE TYPE	ADIH



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

