



Eaton 36TDQSJ25

Eaton Bussmann series medium voltage DIN fuse, 25 A, AC 36 kV, 2", 51 x 537 mm, backup, DIN, with striker

□□□□

PRODUCT NAME	Eaton Bussmann series medium voltage DIN fuse
CATALOG NUMBER	36TDQSJ25
UPC	051712186445
PRODUCT LENGTH/DEPTH	537 mm
PRODUCT HEIGHT	54 mm
PRODUCT WIDTH	51 mm
PRODUCT WEIGHT	2900 g
COMPLIANCES	DIN 43625 VDE 0670-4 IEC 60282-1
CERTIFICATIONS	UL VDE

USED WITH	270303 Fuse clip A3354710 Fuse clip
AMPERAGE RATING	25 A
FUSE INDICATOR	With Striker
FUSE SIZE	51 x 537 mm
BREAKING CAPACITY	35.5 kA
INSTALLATION TECHNIQUE	Air
PERFORMANCE CAT ACCORDING TO IEC 60282-1	Back-up
PRODUCT APPLICATION	Primary side transformer protection
RATED FREQUENCY - MAX	50 Hz
RATED FREQUENCY - MIN	50 Hz
RELEASE CHARACTERISTIC	Other
STANDARD	DIN
UTILIZATION CATEGORY	Other
VOLTAGE TYPE	AC
WITH STRIKER	Yes
CLASS	Class back-up
BARRELS	1
CONSTRUCTION TYPE	Bolt-on
PRE ARC (I ² T)	1.2 x 1000
RESISTANCE	98 Ohms
WATT LOSSES	85 W
FUSE DIAMETER	51 mm
COLOR	Brown
INTERRUPT RATING	35.5 kAIC
CONSTRUCTION SIZE	51 x 537 mm
MOUNTING METHOD	Clip-in
PACKAGING TYPE	Standard
QUANTITY	1
VOLTAGE RATING	36 kV
TYPE	Fuse
SPECIAL FEATURES	Back-up, Transformer protection, Indoor or outdoor use
APPLICATION	• transformer protection • indoor or outdoor

use	
FUSE TYPE	TDQSJ

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

