



□□□□

Eaton 40071352915

Eaton LED drivers including CG-S modules
LED supply and monitoring module V-CG-
SLU-350 (without packing)

□□□□

PRODUCT NAME	Eaton LED drivers including CG-S modules
CATALOG NUMBER	40071352915
PRODUCT LENGTH/DEPTH	55 mm
PRODUCT HEIGHT	40 mm
PRODUCT WIDTH	40 mm
PRODUCT WEIGHT	0.04 kg
CERTIFICATIONS	CE marking



Powering Business Worldwide



LAMP TYPE	LED
NOMINAL VOLTAGE - MAX	240 V
NOMINAL VOLTAGE - MIN	220 V
PROTECTION CLASS	I or II
NOMINAL VOLTAGE RANGE DC - MAX	275 V
NOMINAL VOLTAGE RANGE DC - MIN	176 V
ADDITIONAL DATA LINE NEEDED	No
AMBIENT TEMPERATURE - MAX	50 °C
AMBIENT TEMPERATURE - MIN	-20 °C
CONNECTION TERMINALS (IN)	2.5 mm ²
CONNECTION TERMINALS (OUT)	1.5 mm ²
CONSTANT OUTPUT	Constant current output
CURRENT CONSUMPTION AT 220V DC	54 mA
ENEC CERTIFIED	Yes
HOUSING COLOR	Grey
HOUSING MATERIAL	Flame retardant polycarbonate
INRUSH CURRENT	3 A
LED MODULE LOAD (NUMBER OF LEDS)	1-8 LEDs (rated current 350 mA), series connection (UF = 2,85 ... 3,5 V)
LUMINOUS FLUX Φ_E/Φ_{IN} AT THE END OF RATED OPERATING TIME	100 %
MAXIMAL NUMBER OF MONITORED LUMINAIRES PER CIRCUIT	20
REVERSE-POLARITY PROTECTED TERMINALS (IN)	Yes
SLI-TECHNOLOGY	No
PRODUCT BRANDING	Eaton
DEGREE OF PROTECTION (IP)	IP20
MAXIMAL PERMISSIBLE TEST POINT TEMPERATURE	70 °C

LINE LENGTH - MAX	1 m
OUTPUT POWER - MAX	9.8 W
OPERATING FREQUENCY	60 Hz
OUTPUT CURRENT - MAX	350 mA
OUTPUT VOLTAGE - MAX	28 VDC
POWER CONSUMPTION MAINS OPERATION - APPARENT POWER (VA)	20.9 VA
POWER FACTOR	0.61
STANDBY POWERLOSS AT 230 V / 50 HZ	0.7 W
SUITABLE FOR CONSTANT CURRENT	YES
SUITABLE FOR CONSTANT VOLTAGE	NO
SUITABLE FOR DC- VOLTAGE (PRIMARY SIDE)	YES
CONSTANT LIGHT OUTPUT (CLO)	YES
IFTTT SUPPORT AVAILABLE	NO
DIMMING 0-10 V	NO
DIMMING 1-10 V	NO
DIMMING DALI	NO
DIMMING DMX	NO
DIMMING POTENTIOMETER (INTEGRATED)	NO
DIMMING LINESWITCH	NO
DIMMING MANUFACTURER'S PROPRIETARY SYSTEM	NO
DIMMING MAINS VOLTAGE MODULATION	NO
DIMMING PHASE CUT- OFF	NO
DIMMING PHASE CUT-ON	NO
DIMMING PROGRAMMABLE	NO
DIMMING RF	NO
DIMMING SINE WAVE REDUCTION	NO
POWER CONSUMPTION	12.8 W
SUITABLE FOR OUTDOOR USE	NO
DIMMING TOUCH AND DIM	NO
DIMMING ZIGBEE	NO

