

Eaton 400NHG3B

Fuse-link, low voltage, 400 A, AC 500 V, NH3, gL/gG, IEC, dual indicator

PRODUCT NAME	Eaton Bussmann series low voltage NH Fuse
CATALOG NUMBER	400NHG3B
PRODUCT LENGTH/DEPTH	150 mm
PRODUCT HEIGHT	85 mm
PRODUCT WIDTH	70 mm
PRODUCT WEIGHT	1098 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269-1 IEC 60269-2 DIN 43620

AMPERAGE RATING	400 A
FITTED WITH:	Metal gripping lugs
FUSE SIZE	NH3
CURRENT TYPE	AC
BREAKING CAPACITY	120 kA
RATED SWITCHING CAPACITY	120 kA
RATED VOLTAGE AC	500 V
CLASS	Class gG/gL
FUSE TYPE	Square body with knife blade contact
ACCESSORY/SPARE PART TYPE	SDL-3 Solid link FEH- Fuse extraction handle SD3-SK Shroud kit SD3-PB 2-phase barriers and 2 ganging links TD3-IP20 Triple pole protection kit
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	Blade end
CONSTRUCTION	NH3
CONSTRUCTION SIZE	NH3
FUSE SHAPE	Knife blade contacts Square body
VOLTAGE TYPE	AC
SUITABLE FOR	SD3-D Single pole NH Fuse base Microswitch 170H0235 EBH Size 00 to 4 Horizontal fuse switch-disconnectors TD3-D Triple pole NH Fuse base
MATERIAL	Ceramic body
QUANTITY	3
VOLTAGE RATING	500 V
TYPE	Fuse



APPLICATION

- industrial
- Utilities, Solar,
Wind

**RATED SWITCHING
CAPACITY AC**120 kA

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the
latest product and support
information.

