

Eaton 400PJ31-7

Eaton Bussmann series low voltage british standard fuse, 400A, AC 415 V, V88/J, 38 x 131 mm, gU, 92mm fixing centres, slotted TAGS

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	400PJ31-7
UPC	051712516587
PRODUCT LENGTH/DEPTH	131 mm
PRODUCT HEIGHT	38 mm
PRODUCT WIDTH	38 mm
PRODUCT WEIGHT	301.6 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS IEC 60269 EAC

AMPERAGE RATING	400 A
FITTED WITH:	Slotted tags
CURRENT TYPE	AC
MOUNTING DIMENSION	Other
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	92 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	415 V
CLASS	Class gG/gL
FUSE TYPE	PJ31
UTILIZATION CATEGORY	gU (utility/distribution protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	31 W
CONNECTION	Bolt-on
CONSTRUCTION	BS88/J
CONSTRUCTION SIZE	J
FUSE SHAPE	Dual slotted bolted tags
VOLTAGE TYPE	AC
VOLTAGE RATING	415 V
TYPE	Fuse
APPLICATION	feeder pillars
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk251033en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

