



## Eaton 500002FULL-0002

Eaton Conventional bell, Alarms & signalling devices, Fulleon, FB Bell, Electronic solenoid, 6", 12V DC, Grey gong

□□□□

<b>PRODUCT NAME</b>	Eaton FB Bell
<b>CATALOG NUMBER</b>	500002FULL-0002
<b>PRODUCT LENGTH/DEPTH</b>	85 mm
<b>PRODUCT HEIGHT</b>	155 mm
<b>PRODUCT WIDTH</b>	155 mm
<b>PRODUCT WEIGHT</b>	1.1 kg
<b>COMPLIANCES</b>	EN



Powering Business Worldwide

□□□□

<b>COLOR HOUSING</b>	Grey
<b>MATERIAL HOUSING</b>	Plastic
<b>SOUND OUTPUT</b>	95 dB
<b>NOMINAL VOLTAGE</b>	12 V
<b>TYPE OF CURRENT</b>	DC
<b>ELECTRICITY CONSUMPTION</b>	0.065 A
<b>MOUNTING METHOD</b>	Surface mounted (plaster)
<b>NUMBER OF MODULES (MODULE SYSTEM)</b>	0
<b>WIDTH IN NUMBER OF MODULAR SPACINGS</b>	0
<b>ADDRESSING MODE</b>	Hard addressing
<b>ALARM CURRENT - MAX</b>	65 mA
<b>ALARM CURRENT - MIN</b>	55 mA
<b>CONSTRUCTION MATERIAL</b>	PC
<b>EN CERTIFIED TONES</b>	0
<b>HUMIDITY (NON CONDENSING) - MAX</b>	95 %
<b>HUMIDITY (NON CONDENSING) - MIN</b>	0 %
<b>OPERATING TEMPERATURE - MAX</b>	55 °C
<b>OPERATING TEMPERATURE - MIN</b>	-10 °C
<b>STANDBY CURRENT</b>	0
<b>SYSTEM TYPOLOGY</b>	Conventional (Non-addressable)
<b>TONES</b>	1
<b>VOICE TONES</b>	No
<b>PRODUCT BRANDING</b>	Eaton
<b>DEGREE OF PROTECTION</b>	IP21
<b>CABLE ENTRY</b>	Rear
<b>SYSTEM WIRING</b>	0.28 mm - 2.5 mm

□□

