

## Eaton 500NHG3B

Eaton Bussmann series low voltage NH Fuse,  
Live gripping lug, 500V, 500A, 120 kAIC,  
Combination fuse status indicator, fuse,  
Blade end connection, Class C gL/gG,  
Square-body with knife blade contact,  
Ceramic body

PRODUCT NAME	Eaton Bussmann series low voltage NH Fuse
CATALOG NUMBER	500NHG3B
UPC	051712626248
PRODUCT LENGTH/DEPTH	150 mm
PRODUCT HEIGHT	86 mm
PRODUCT WIDTH	71 mm
PRODUCT WEIGHT	1027 g
COMPLIANCES	RoHS Compliant CE Marked
CERTIFICATIONS	IEC 60269-1 IEC 60269-2 DIN 43620

AMPERAGE RATING	500 A
FITTED WITH:	Metal gripping lugs
FUSE SIZE	NH01
CURRENT TYPE	AC
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
RATED SWITCHING CAPACITY	120 kA
RATED VOLTAGE AC	500 V
CLASS	Class gG/gL
FUSE TYPE	Square body with knife blade contact
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	Blade end
CONSTRUCTION	NH3
CONSTRUCTION SIZE	NH3
FUSE SHAPE	Knife blade contacts Square body
VOLTAGE TYPE	AC
SUITABLE FOR	Microswitch 170H0235
MATERIAL	Ceramic body
QUANTITY	3
VOLTAGE RATING	500 V
TYPE	fuse
SPECIAL FEATURES	Live gripping lug
APPLICATION	<ul style="list-style-type: none"><li>• industrial</li><li>• Utilities, Solar, Wind</li></ul>



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

