



□□□□□

Eaton 500NHG4G

Eaton Bussmann series low voltage NH Fuse, 500V, 500A, 120 kAIC, Top fuse status indicator, fuse, Class C gL/gG

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage NH Fuse
CATALOG NUMBER	500NHG4G
UPC	051712295291
PRODUCT LENGTH/DEPTH	222 mm
PRODUCT HEIGHT	136 mm
PRODUCT WIDTH	116 mm
PRODUCT WEIGHT	2240 g
COMPLIANCES	RoHS Compliant

□□□□

AMPERAGE RATING	500 A
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
RATED SWITCHING CAPACITY	120 kA
RATED VOLTAGE AC	500 V
CLASS	Class C gL/gG
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	37 W
CONSTRUCTION	NH4
CONSTRUCTION SIZE	NH4
FUSE SHAPE	Square body Slotted blade contacts
VOLTAGE TYPE	AC
PACKAGING TYPE	Standard
VOLTAGE RATING	500 V
TYPE	Fuse
APPLICATION	industrial
RATED SWITCHING CAPACITY AC	120 kA

□□□□:

□□□□:

□□□:

□□:

□□

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-nh-fuse-declaration-of-conformity-uk251024en.pdf](#)