



Eaton 500R20

Eaton Bussmann series low voltage british standard fuse, 500A, AC 660 V, 74 x 112 mm, gL/gG

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	500R20
PRODUCT LENGTH/DEPTH	112 mm
PRODUCT HEIGHT	75 mm
PRODUCT WIDTH	75 mm
PRODUCT WEIGHT	932 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS88 IEC 60269 EAC

□□□□

AMPERAGE RATING	500 A
CURRENT TYPE	AC
MOUNTING DIMENSION	M8
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	94 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	660 V
CLASS	Class gG/gL
FUSE TYPE	R20
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	38 W
CONNECTION	94 mm fixing centre
CONSTRUCTION	BS88
CONSTRUCTION SIZE	Other
FUSE SHAPE	Offset slotted bolted tags
VOLTAGE TYPE	AC
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□

DECLARATIONS OF
CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250882en.pdf](#)

