



Eaton 50AFE

Eaton Bussmann series high speed British standard fuse, 50 A, 690 V, None, 76 mm CC, aR (accompanied semiconductor protection)

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	50AFE
UPC	051712292306
PRODUCT LENGTH/DEPTH	100 mm
PRODUCT HEIGHT	22 mm
PRODUCT WIDTH	187 mm
PRODUCT WEIGHT	45.8 g
COMPLIANCES	Contact factory RoHS Compliant



AMPERAGE RATING	50 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
RATED SWITCHING CAPACITY	200 kA
RATED VOLTAGE AC	690 V
RATED VOLTAGE DC	500 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	76 mm
MOUNTING DIMENSION	M8
CURRENT TYPE	AC/DC
CLASS	Class aR
WATT LOSSES	11 W
FUSE SHAPE	Offset slotted bolted tags
COLOR	None
CONSTRUCTION SIZE	Other
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	AFE
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

