


Eaton 50NHG000B-400

Fuse-link, LV, 50 A, AC 400 V, NH000, gL/gG, IEC, dual indicator, live gripping lugs

PRODUCT NAME	Eaton Bussmann series low voltage NH Fuse
CATALOG NUMBER	50NHG000B-400
UPC	051712233347
PRODUCT LENGTH/DEPTH	79 mm
PRODUCT HEIGHT	51 mm
PRODUCT WIDTH	21 mm
PRODUCT WEIGHT	119 g
COMPLIANCES	RoHS Compliant CE Marked
CERTIFICATIONS	IEC 60269 IEC 60269-2 EAC VDE

AMPERAGE RATING	50 A
CURRENT TYPE	AC
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
RATED SWITCHING CAPACITY	120 kA
RATED VOLTAGE AC	400 V
CLASS	Class gG/gL
FUSE TYPE	Square body with knife blade contact
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	3.4 W
CONNECTION	Blade end
CONSTRUCTION	NH000
CONSTRUCTION SIZE	NH000
FUSE SHAPE	Square body Knife blade contacts
VOLTAGE TYPE	AC
PACKAGING TYPE	Standard
QUANTITY	3
VOLTAGE RATING	400 V
TYPE	Fuse
APPLICATION	industrial
RATED SWITCHING CAPACITY AC	120 kA



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

