



## Eaton 550075FULL-0228X

Eaton, Alarms & signalling devices, Fulleon, Askari Compact sounder, White (W1) housing, No base (AC/SV/GW/S)

□□□□

<b>PRODUCT NAME</b>	Eaton Askari Compact Alarm sounder
<b>CATALOG NUMBER</b>	550075FULL-0228X
<b>PRODUCT LENGTH/DEPTH</b>	36 mm
<b>PRODUCT HEIGHT</b>	86 mm
<b>PRODUCT WIDTH</b>	86 mm
<b>PRODUCT WEIGHT</b>	0.11 kg
<b>CERTIFICATIONS</b>	Not Applicable



Powering Business Worldwide

□□□□

<b>NUMBER OF TONES</b>	32
<b>COLOR HOUSING</b>	White
<b>MATERIAL HOUSING</b>	Plastic
<b>SOUND OUTPUT</b>	97 dB
<b>NOMINAL VOLTAGE</b>	24 V
<b>TYPE OF CURRENT</b>	DC
<b>ELECTRICITY CONSUMPTION</b>	0.035 A
<b>ADDRESSING MODE</b>	Hard addressing
<b>ALARM CURRENT</b>	35 mA
<b>CONSTRUCTION MATERIAL</b>	ABS/FR
<b>EN CERTIFIED TONES</b>	6
<b>OPERATING TEMPERATURE - MAX</b>	55 °C
<b>OPERATING TEMPERATURE - MIN</b>	-10 °C
<b>SYSTEM TOPOLOGY</b>	Conventional (Non-Addressable)
<b>TONES</b>	32
<b>VOICE TONES</b>	No
<b>PRODUCT BRANDING</b>	Eaton
<b>HUMIDITY (NON CONDENSING) - MAX</b>	95 %
<b>HUMIDITY (NON CONDENSING) - MIN</b>	0 %
<b>DEGREE OF PROTECTION</b>	IP21
<b>EN CERTIFICATION STANDARDS</b>	EN54 Pt3 (Fire Alarm Sounders)
<b>CABLE ENTRY</b>	Rear
<b>SYSTEM WIRING</b>	0.28 - 2.5 mm

□□

