



□□□□□

Eaton 560SJ31-6

Eaton Bussmann series low voltage british standard fuse, 560A, AC 415 V, V88/J, 73 x 129 mm, gU, 92mm fixing centres, slotted TAGS

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	560SJ31-6
PRODUCT LENGTH/DEPTH	129 mm
PRODUCT HEIGHT	74 mm
PRODUCT WIDTH	74 mm
PRODUCT WEIGHT	748 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS IEC 60269 EAC

□□□□

AMPERAGE RATING 560 A

FITTED WITH: Slotted tags

CURRENT TYPE AC

MOUNTING DIMENSION Other

**CENTER-TO-CENTER
DISTANCE OF
CONNECTIONS** 92 mm

BREAKING CAPACITY 80 kA

**RATED SWITCHING
CAPACITY** 80 kA

RATED VOLTAGE AC 400 V

CLASS Class gG/gL

FUSE TYPE SJ31

UTILIZATION CATEGORY gU (utility/distribution protection)

COLOR None

INTERRUPT RATING 80 kAIC

FUSE INDICATOR None

**INSULATED METAL
GRIPPING LUGS (IMGL)** No

WATT LOSSES 38 W

CONNECTION Bolt-on

CONSTRUCTION BS88/J

CONSTRUCTION SIZE J

FUSE SHAPE Dual slotted bolted tags

VOLTAGE TYPE AC

VOLTAGE RATING 415 V

TYPE Fuse

APPLICATION feeder pillars

**FUSE SYSTEM
(ACCORDING TO IEC
60269)** Fuse system E

□□

DECLARATIONS OF
CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250880en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

