



Eaton 5SC1500G

Eaton 5SC UPS, 1500 VA, 1050 W, C14 input, Global, Outputs: (8) C13

Specifications

PRODUCT NAME	Eaton 5SC UPS
CATALOG NUMBER	5SC1500G
UPC	743172045133
PRODUCT LENGTH/DEPTH	16.1 in
PRODUCT HEIGHT	8.2 in
PRODUCT WIDTH	5.9 in
PRODUCT WEIGHT	33.5 lb
COMPLIANCES	FCC Part 15 CISPR22 Class A / FCC part 15 Class A
CERTIFICATIONS	EN 62040-2:2006

□□□□	
TOPOLOGY	Line-interactive
FORM FACTOR	Tower
CONSTRUCTION TYPE	Free standing model
COLOR	Black
VA RATING	1500 VA
WATTAGE	900 W
SURGE PROTECTION	Yes
INPUT CONNECTION	C14
INPUT NOMINAL VOLTAGE	230V
INPUT FREQUENCY RANGE	45-55 Hz (50 Hz system), 55-65 Hz (60 Hz system)
RECEPTACLE	(8) C13
NUMBER OF OUTPUTS C13	8
OUTPUT NOMINAL VOLTAGE	220/230/240V
RUNTIME GRAPH	\$row.attributeValue.cdata
BATTERY MANAGEMENT	ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)
BATTERY TYPE	Sealed, lead-acid
EXTENDED BATTERY CAPABILITY	Not available
STANDARD FACTORY WARRANTY	• 2-YEAR FACTORY WARRANTY • -2 years • -Parts, electronics, and batteries coverage • -Standard ground shipping • -Technical support
EXTENDED SERVICE PLANS	• ADVANCED DEPOT EXCHANGE • -5-YEAR DEPOT REPAIR: 5SW5Y-1750UC • -Expedited parts coverage for 5 years • -Parts, electronics and UPS batteries coverage • -Next business day

- shipping
- -Technical support

COMMUNICATION	RS-232 (RJ45) port; USB port as standard (HID). 6-foot RS-232 and USB cables included
SOFTWARE COMPATIBILITY	Eaton Intelligent Power Manager
USER INTERFACE	LCD display
NOISE LEVEL	<40 dB at 1 meter
RELATIVE HUMIDITY	0-95% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
EFFICIENCY AT MAX. LOAD	94%
INPUT VOLTAGE RANGE	184-276 Vac
QUANTITY	1

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

